



KINTEK PRESS

Contact us for more catalogs of

# KINTEK PRESS

> > >



: PCVM



|               |                                         |
|---------------|-----------------------------------------|
|               | PCVM - 10 T                             |
|               | 0 - 10 . 0                              |
|               | 5 0 0 ° C                               |
|               | 1 8 0 x 1 8 0 mm , 2 0 0 x 2 0 0 mm ( ) |
|               | SUS 3 0 4 ( )                           |
|               | 4 0 0 x 4 0 0 x 4 0 0 mm                |
|               | 3 0 0 x 3 5 0 mm                        |
|               | - 0 . 1 MP a                            |
| ( L x W x H ) | 4 5 0 x 5 5 0 x 8 5 0 mm                |
|               | 2 2 0 V 5 0 Hz ( 1 1 0 V )              |

: P C S M



|  | PCSM - 30 T 3030                           | PCSM - 40 T 4040                           |
|--|--------------------------------------------|--------------------------------------------|
|  | 0 - 30 . 0                                 | 0 - 40 . 0                                 |
|  | 130mm ( d )                                | 130mm ( d )                                |
|  |                                            |                                            |
|  | - 300 . 0 C / 500 . 0 C                    | - 300 . 0 C                                |
|  |                                            |                                            |
|  | [                      ]                   | [                      ]                   |
|  | 300×300mm ( M×N )                          | 400×400mm ( M×N )                          |
|  | 380×350X600mm ( K×P×H )                    | 500×480×650 ( K×P×H )                      |
|  | 700×400×600mm ( L×W×H )                    | 800×480×650 ( L×W×H )                      |
|  | 3000W ( 220V / 110V                      ) | 5000W ( 220V / 110V                      ) |
|  | 260 Kg                                     | 460 Kg                                     |
|  |                                            |                                            |

: PCY



|  | PCY - 5T1212          | PCY - 10T1818         | PCY - 10T2020         | PCY - 15T3030         |
|--|-----------------------|-----------------------|-----------------------|-----------------------|
|  | 0 - 5 . 0             | 0 - 10 . 0            | 0 - 10 . 0            | 0 - 15 . 0            |
|  | 50 mm (               | 65 mm ( d             | 65 mm (               | 95 mm ( d )           |
|  |                       |                       |                       |                       |
|  | - 300 . 0C / 500 . 0C | - 300 . 0C / 500 . 0  | - 300 . 0C / 500 . 0  | - 300 . 0C / 500 . 0C |
|  |                       |                       |                       |                       |
|  | [                     | [ ]                   | [ ]                   | [ ]                   |
|  | 120×120mm (M×N)       | 180×180mm             | 200×200mm             | 300×300mm (M×N)       |
|  | 140×140×60mm          | 180×180×60mm          | 200×200×60mm          | 300×300×65mm          |
|  | 250×230×390mm (L×W×H) | 290×290×420mm (L×W×H) | 320×290×420mm (L×W×H) | 450×420×450mm (L×W×H) |
|  | 700W (220V / 110V)    | 1000W (220V / 110V)   | 1200W (220V / 110V)   | 3000W (220V / 110V)   |
|  | 55 Kg                 | 90 Kg                 | 95 Kg                 | 180 Kg                |
|  |                       |                       |                       |                       |

: C P C L



|               |                          |
|---------------|--------------------------|
|               | PC - 900 L               |
|               | 0 - 5 . 0                |
|               | 8 0 mm                   |
|               | 1 0 0 0 ° C ( )          |
|               | ( )                      |
|               | 1 0 - 3 0 mm ( )         |
|               | 5 0 x 9 0 mm ( )         |
|               | 6 0 mm ( )               |
| ( L x W x H ) | 4 0 0 x 3 8 0 x 7 8 0 mm |
|               | 2 2 0 V 5 0 H z ( )      |

## 24 T 30 T 60 T

: PCH



,  
.

!

|  | PCH - 24 T1010          | PCH - 30 T2020          | PCH - 30 T1818          |
|--|-------------------------|-------------------------|-------------------------|
|  | 0 - 24 . 0              | 0 - 30 . 0              | 0 - 30 . 0              |
|  | 95mm ( d )              | 110mm ( d )             | 150mm ( d )             |
|  |                         |                         |                         |
|  | - 300 . 0 C / 500 . 0 C | - 300 . 0 C / 500 . 0 C | - 300 . 0 C / 500 . 0 C |
|  |                         |                         |                         |
|  | [ ]                     | [ ] [ ]                 | [ ] [ ]                 |
|  | 100×100mm ( M×N ) ( )   | 200×200mm ( M×N )       | 180×180mm ( M×N )       |
|  | 245×175×500mm ( K×P×H ) | 405×260×525mm ( K×P×H ) | 405×260×525mm ( K×P×H ) |
|  | 500×175×500mm ( L×W×H ) | 950×260×525mm ( L×W×H ) | 950×260×525mm ( L×W×H ) |
|  | 600W ( 220V / 110V )    | 1200W ( 220V / 110V )   | 1000W ( 220V / 110V )   |
|  | 60 Kg                   | 180 Kg                  | 180 Kg                  |

: PCV



|  | PCV - 10T1818                       | PCV - 10T2020                       |
|--|-------------------------------------|-------------------------------------|
|  | 0 - 10 . 0                          | 0 - 10 . 0                          |
|  |                                     |                                     |
|  | 5 0 0 ° C                           | 5 0 0 ° C                           |
|  | 1 8 0 × 1 8 0 mm                    | 2 0 0 × 2 0 0 mm                    |
|  | SUS 3 0 4 ( )                       | SUS 3 0 4 ( )                       |
|  | 4 0 0 × 4 0 0 × 4 0 0 mm            | 4 0 0 × 1 0 0 × 4 0 0 mm            |
|  | 3 0 0 × 3 5 0 mm                    | 3 0 0 × 3 5 0 mm                    |
|  | - 0 . 1 MP a                        | - 0 . 1 MP a                        |
|  | 4 5 0 × 5 5 0 × 8 5 0 ( L × W × H ) | 4 5 0 × 5 5 0 × 8 5 0 ( L × W × H ) |
|  | 2 2 0 V 5 0 Hz ( 1 1 0 V )          | 2 2 0 V 5 0 Hz ( 1 1 0 V )          |

: P C S E



3 0 0 ° C

|  | PCSE - 40T4040                  | PCSE - 30T3030                  |
|--|---------------------------------|---------------------------------|
|  | 0 - 40 . 0                      | 0 - 30 . 0                      |
|  | -                               | -                               |
|  | - 300 . 0 ° C                   | - 300 . 0 ° C / 500 . 0 ° C ( ) |
|  |                                 |                                 |
|  | [ ]                             | [ ]                             |
|  | 400 × 400mm ( M × N )           | 300 × 300mm ( M × N )           |
|  | 500 × 480 × 650mm ( K × P × H ) | 380 × 350 × 600mm ( K × P × H ) |
|  | 850 × 480 × 650mm ( L × W × H ) | 700 × 400 × 600mm ( L × W × H ) |
|  | 5500W ( 220V / 110V )           | 3500W ( 220V / 110V )           |
|  | 480 Kg                          | 280 Kg                          |

: P P L



|  |                                  |
|--|----------------------------------|
|  | PP - 900 L                       |
|  | 0 - 10 T                         |
|  | - -                              |
|  | 1 ~ 9999 ( " " )                 |
|  | 80 mm                            |
|  | 1000                             |
|  | ( )                              |
|  | 10 - 30 mm                       |
|  | 50 x 90 mm                       |
|  | 60 mm                            |
|  | 400 x 380 x 780 ( L x W x H ) mm |
|  | 220 V 50 Hz                      |
|  |                                  |

: PCAH



|  | PCAH - 25T1818 / 1818G    | PCAH - 25T2020 / 2020G    | PCAH - 30T3030 / 3030G    | PCAH - 40T4040 / 4040G    |
|--|---------------------------|---------------------------|---------------------------|---------------------------|
|  | 0 - 25 . 0                | 0 - 25 . 0                | 0 - 30 . 0                | 0 - 40 . 0                |
|  | -                         | -                         | -                         | -                         |
|  | - 300 . 0 / 500 . 0       | - 300 . 0 / 500 . 0       | - 300 . 0 / 500 . 0       | - 300 . 0                 |
|  |                           |                           |                           |                           |
|  | [                         | [                         | [                         | [                         |
|  | ]                         | ]                         | ]                         | ]                         |
|  | 180 × 180mm (M×N)         | 200 × 200mm (M×N)         | 300 × 300mm (M×N)         | 400 × 400mm (M×N)         |
|  | 300 × 390 × 560mm (L×W×H) | 300 × 390 × 560mm (L×W×H) | 400 × 490 × 580mm (L×W×H) | 500 × 550 × 620mm (L×W×H) |
|  | 1700W (220V / 110V)       | 1700W (220V / 110V)       | 3500W (220V / 110V)       | 5500W (220V / 110V)       |
|  | 140 Kg                    | 140 Kg                    | 280 Kg                    | 480 Kg                    |

: PHA



|  |                                  |
|--|----------------------------------|
|  | PHA                              |
|  | 0 - 10 T                         |
|  | -                                |
|  | 1 ~                              |
|  | 80 mm                            |
|  | 1000                             |
|  | ( )                              |
|  | 10 - 30 mm                       |
|  | 50 * 90 mm ( )                   |
|  | 60 mm                            |
|  | 400 * 380 * 780 ( L * W * H ) mm |
|  | 220 V 50 Hz                      |
|  |                                  |



K i n t e k   P r e s s

W h a t s A p p