



K I N T E K P R E S S

C o n t a c t u s f o r m o r e c a t a l o g s o f

KINTEK PRESS

> > >



2T

Kbr Ftir

: KT - KBP



FTIR

KBr

KINTEK 2T

	PCKBR - 2T
(T)	0 - 2 (30Mpa)
	4.5 mm
	1 MPa / 10
	4.5 mm
	2
(W × D)	54 × 55 mm
(W × L × H)	100 × 220 × 220 mm
(kg)	4.8 kg

: P C M P



	PCMP - 2T	PCMP - 5T	PCMP - 12T	PCMP - 15T	PCMP - 24T	PCMP - 30T	PCMP - 40T
	0 - 2T (25 MP a)	0 - 5T (0 - 31 . 4 M)	0 - 12T (0 - 30 M F)	0 - 15T (0 - 30 M F)	0 - 24T (0 - 34 M F)	0 - 30T (0 - 31 . 5)	0 - 40T (0 - 30 M P a)
	32 mm (d)	45 mm (d)	70 mm (d)	80 mm (d)	95 mm (d)	110 mm (d)	130 mm (d)
(T)	30 mm	40 mm	50 mm				
	1 MP a / 10						
	50 mm (D)	80 mm (D)	80 mm (D)	90 mm (D)	105 mm (D)	120 mm (D)	140 mm (D)
	2	2	2	2	Four	Four	Four
	85 × 120 mm (M × N)	96 × 130 mm (M × N)	96 × 130 mm (M × N)	140 × 150 mm (M × N)	80 × 150 mm (M × N)	92 × 160 mm (M × N)	106 × 185 mm (M × N)
	210 × 150 × 350 mm (L × W × H)	225 × 155 × 380 mm (L × W × H)	225 × 155 × 380 mm (L × W × H)	245 × 175 × 390 mm (L × W × H)	245 × 175 × 415 mm (L × W × H)	275 × 195 × 420 mm (L × W × H)	295 × 215 × 500 mm (L × W × H)
	12 Kg	28 Kg	28 Kg	38 Kg	42 Kg	56 Kg	75 Kg

: PCF



	PCF - 15T	PCF - 24T	PCF - 30T	PCF - 40T	PCF - 60T
	0 - 15T (0 - 30 MP a)	0 - 24T (0 - 34 MP a)	0 - 30T (0 - 31 . 5 MP	0 - 40T (0 - 30 MP a)	0 - 60T (0 - 34 MP a)
	80mm(d)	95mm(d)	110mm(d)	130mm (d)	150mm (d)
" (T) "	30mm	30mm	40mm	50mm	50mm
	()	()	()	()	()
	1 MP a / 10				
	90mm(D)	105mm (D)	120mm (D)	140mm (D)	160mm(D)
	4	4	4	4	Four
	80 × × 130 mm(M× N)	112 × 160 mm(M× N)	112 × 160 mm(M× N)	126 × 185 mm(M× N)	185 × 250 mm(M× N)
	260 × 175 × 395 mm(H)	305 × 195 × 425 mm(H)	305 × 195 × 425 mm(H)	355 × 215 × 505 mm(H)	405 × 240 × 565 mm(L × W× H)
	42 Kg	65 Kg	65 Kg	90 Kg	120 Kg

()	(MP a)
1	0 . 75
3	2 . 2
5	3 . 7
10	7 . 5
12	9
15	11 . 3
20	15
30	22 . 5

40

30

: 3.5 MPa

: PT10



	PT10
	3Cr13()
	10, 12, 14, 15, 16, 18, 19(d)
	120*200*280mm(L*W*H)
	10kg

: PC2NS



CR2032, LR4

, R & D

!

	PC2NS
	0 - 2T (0 - 25 MPa)
	32mm(d)
	0.00 - 40.00MPa
	CR20
	CR16, CR20, CR24, CR30
	0.8 - 1.2
	CR16, CR20, CR24, CR30
	0.4
	210 * 165 * 290mm(L X * W * H)
	1.2 Kg

: PC2N



CR2032, LR44

	PC - 2 N
	0 - 2 T (0 - 25 MP a)
	32 mm(d)
	CR20
	CR16, CR20, CR24, CR30
	0.8 - 1.2
	CR16, CR20, CR24, CR30
	0.4
	210 * 165 * 290mm(L X * W * H)
	12 Kg

: PCBP



	PCBP-2T ()		PCBP-1.5T ()
	0-2T (0-25 MPa)		50-1500kg
	32mm(d)		-
			0-999
	CR20	LCD	4.3 LCD
	CR16, CR20, CR24, CR30option		CR16, CR20, CR24, CR30
	0.8-1.2		CR16, CR20, CR24, CR30
	CR16, CR20, CR24		CR20
			220x240x380(LxWxH)
	210x165x290mm(LxWxH)		220V(50Hz/60Hz)
	12Kg		35kg

: PCEA



KINTEK

	PCEA-12T	PCEA-20T	PCEA-30T	PCEA-40T	PCEA-60T	PCEA-100T	PCEA-150T
	0.2-12.0	1-20.0	1-30.0	1-40.0	1-60.0	1-100.0	1-150.0
	4.3 LCD			7 LCD			
	100,000						
	(T) 30mm			50mm			
(MxN)	110x140mm	140x160mm	140x160mm	175x180mm	185x220mm	185x250mm	200x260mm
(LxWxH)	185x320x360mm	230x390x42	230x390x42	280x460x55	300x520x58	330x580x62	400x620x620mm
	240W(220V/110V	550W(220V/110V)			1500W(220V/110V)		
	50 Kg	90Kg	150Kg	180Kg	240Kg	380Kg	

: P C E S



	PCES - 40T	PCES - 65T	PCES - 100T	PCES - 150T	PCES - 200T
	0 - 40	0 - 65	1 - 100	1 - 150	1 - 200
	130mm(d)	160mm(d)	200mm(d)	250mm(d)	290mm(d)
	7 LCD				
	(150mm	50mm	50mm	50mm	50mm
	160×300mm(M×N)	220×300mm(M×N)	260×250mm(M×N)	285×290mm(M×N)	290×300mm(M×N)
	500×700×800mm(L	580×700×800mm(L	850×500×950mm(L	950×600×1000mm(L	1000×650×1050mm(L×W×H)
	1500W(220V / 110V)				
	200kg	280kg	520kg	620kg	850kg

X r f

K b r F t i r

: P C P E



	PCPE - 20T	PCPE - 30T	PCPE - 40T	PCPE - 60T
	0 - 20T (0 - 28 MP a)	0 - 30T (0 - 31. 5 0 - 40T (0 - 30MP	0 - 60T (0 - 33 MP a)	
	95 mm(d)	110 mm(d)	130 mm(d)	150 mm(d)
	0. 00 - 40. 00 MP a	0. 00 - 40. 00 MP a	0. 00 - 40. 00 MP a	0. 00 - 40. 00 MP a
(T)	30 mm()	40 mm()	50 mm()	50 mm()
	1 MP a / 10	1 MP a / 10	1 MP a / 10	1 MP a / 10
	/	/	/	/
	/	/	/	/
	105 mm(D)	120 mm (D)	140 mm(D)	160 mm(D)
	4	4	4	4
	80 × 150 mm(M × N)	92 × 160 mm(M × N)	115 × 185 mm(M × N)	185 × 250 mm(M × N)
	245 × 415 × 415 mm(L × W × H)	275 × 430 × 420 mm(L × W × H)	295 × 450 × 500 mm(L × W × H)	405 × 470 × 565 mm(L × W × H)
	220V (50Hz / 60Hz)	220V (50Hz / 60	220V (50Hz / 60	220V (50Hz / 60 Hz)
	58 Kg	72 Kg	92 Kg	140 Kg

1 []	1. 41 [MP a]
2 []	2. 82 [MP a]
3 []	4. 23 [MP a]
5 []	7. 06 [MP a]
8 []	11. 3 [MP a]

10 []	14.1 [MPa]
12 []	17 [MPa]
15 []	22.6 [MPa]
20 []	28 [MPa]
:	35 MPa

: PP2N



300 ~ 600

!

	PP2N
	50 - 1500 kg
	-
	0 - 999
LCD	4.3 LCD
	CR16, CR20, CR24, CR30
	CR16, CR20, CR24, CR30
	CR20
	220 * 240 * 380 (L * W * H)
	220V (50Hz / 60Hz)
	35 kg

X r f K b r

: P M X A



K i n T e k X R F

X R F / I P

	P M X A - 3 0 T	P M X A - 4 0 T	P M X A - 6 0 T
	1 - 3 0 . 0	0 - 4 0 . 0	0 - 6 0 . 0
	- - - - -	- - - - -	- - - - -
	0 - 9 9 9	0 - 9 9 9	0 - 9 9 9
	4 . 3 L C D	4 . 3 L C D	4 . 3 L C D
	1 0 0 , 0 0 0	1 0 0 , 0 0 0	1 0 0 , 0 0 0
	/ / (1	/ / (1	/ / (1
	4 0 m m ()	4 0 m m ()	4 0 m m ()
	4 4 0 C	4 4 0 C	4 4 0 C
(L × W × H)	2 5 0 × 3 9 0 × 4 6 0 m m	2 8 0 × 4 6 0 × 5 5 0 m m	3 0 0 × 5 2 0 × 5 8 0 m m
	5 5 0 W (2 2 0 V / 1 1 0 V)	5 5 0 W (2 2 0 V / 1 1 0 V)	5 5 0 W (2 2 0 V / 1 1 0 V)
	1 2 0 K g	1 5 0 K g	1 8 0 K g

: PCG



	PCG - 25T1818	PCG - 25T2020
	0 - 25T	0 - 25T
	-	-
	0 - 999.59 ()	0 - 999.59 ()
	500	500
	180×180mm	200×200mm
	St ' s 304	St ' s 304
	780×650×700mm	780×650×700mm
	240×260mm	240×260mm
	- 0.1 MPa	- 0.1 MPa
	1200×950×1800mm(L×W×H)	1200×950×1800mm (L×W×H)
	220V 50Hz	220V 50Hz



K i n t e k P r e s s

W h a t s A p p