



KINTEK PRESS

Contact us for more catalogs of

KINTEK PRESS

> > >



: PCIH



(WIP) . ASME

100 °C , .

	PCIH-20T	PCIH-40T	PCIH-60T	PCIH-100T
	0-20T	0-40T	0-60.0	0-100
	130mm (	150mm (	200mm	220mm (d)
	-	-		
	1 ~ 999	1 ~ 999	1 ~ 999	1 ~ 999
	7 LCD	7 LCD	7 LCD	7 LCD
	-200.0C	-200.0C	-200.0C	-200.0C
	300MPa	300MPa	300MPa	500MPa
	30×150mm (M×N)	40×150mm (M×N)	×50×150 (M×N)	×50×150 (M×N)
(T)	50mm	50mm	50mm	50mm



K i n t e k P r e s s

W h a t s A p p