

24T 30T 60T

: PCH



	PCH- 24T1010	PCH- 30T2020	PCH- 30T1818
	0 - 24 . 0	0 - 30 . 0	0 - 30 . 0
	95 mm (d)	110 mm (d)	150 mm (d)
	- 300 . 0C / 500 . 0C	- 300 . 0C / 500 . 0C	- 300 . 0C / 500 . 0C
	[]	[] []	[] []
	100×100mm(M×N) ()	200×200mm(M×N)	180×180mm(M×N)
	245×175×500mm(K×P×H)	405×260×525mm(K×P×H)	405×260×525mm(K×P×H)
	500×175×500mm(L×W×H)	950×260×525mm(L×W×H)	950×260×525mm(L×W×H)
	600W(220V / 110V)	1200W(220V / 110V)	1000W(220V / 110V)
	60 Kg	180 Kg	180 Kg