

: P C S E



3 0 0 ° C

	PCSE - 40T4040	PCSE - 30T3030
	0 - 40 . 0	0 - 30 . 0
	-	-
	- 300 . 0 ° C	- 300 . 0 ° C / 500 . 0 ° C ()
	[]	[]
	400 × 400mm (M × N)	300 × 300mm (M × N)
	500 × 480 × 650mm (K × P × H)	380 × 350 × 600mm (K × P × H)
	850 × 480 × 650mm (L × W × H)	700 × 400 × 600mm (L × W × H)
	5500W (220V / 110V)	3500W (220V / 110V)
	480 Kg	280 Kg