

: PCAH



	PCAH- 25T1818/1818G	PCAH- 25T2020/2020G	PCAH- 30T3030/3030G	PCAH- 40T4040/4040G
	0- 25. 0	0- 25. 0	0- 30. 0	0- 40. 0
	-	-	-	-
	- 300. 0 / 500. 0	- 300. 0 / 500. 0	- 300. 0 / 500. 0	- 300. 0
	[[[[] [
	180×180mm(M×N)	200×200mm(M×N)	300×300mm(M×N)	400×400mm(M×N)
	300×390×560mm(L×W×H)	300×390×560mm(L×W×H)	400×490×580mm(L×W×H)	500×550×620mm(L×W×H)
	1700W(220V/110V)	1700W(220V/110V)	3500W(220V/110V)	5500W(220V/110V)
	140 Kg	140 Kg	280 Kg	480 Kg