

: P MH



(500 ° C) ,

	- 300. 0 ° C (500 ° C)
	: 440 C
	HRC 60 - HRC 62
	10, 13, 15, 20, 30, 40 mm ()
	40 mm (N)
	78 * 138 mm, 90 * 138 mm (L * * H)
	300 W (220 V / 110 V)
	9 k g

[Mpa]	50	100	300	400	600	800	1000	1200	1500
8 T	0. 25	0. 5	1. 5	2. 01	3. 01	4. 02	5. 02	6. 03	7. 53
10 T	0. 39	0. 78	2. 35	3. 14	4. 71	6. 28	7. 85	9. 42	11. 7
12 T	0. 56	1. 13	3. 39	4. 52	6. 78	9. 04	11. 3	13. 5	16. 9
13 T	0. 66	1. 32	3. 98	5. 3	7. 96	10. 6	13. 2	15. 9	19. 9
15 T	0. 88	1. 76	5. 3	7. 06	10. 6	14. 1	17. 6	21. 2	26. 5
20 T	1. 57	3. 14	9. 42	12. 5	18. 8	25. 1	31. 4	37. 6	47. 1