

: PCV



|  | PCV - 10T1818                       | PCV - 10T2020                       |
|--|-------------------------------------|-------------------------------------|
|  | 0 - 10 . 0                          | 0 - 10 . 0                          |
|  |                                     |                                     |
|  | 5 0 0 ° C                           | 5 0 0 ° C                           |
|  | 1 8 0 × 1 8 0 mm                    | 2 0 0 × 2 0 0 mm                    |
|  | SUS 3 0 4 ( )                       | SUS 3 0 4 ( )                       |
|  | 4 0 0 × 4 0 0 × 4 0 0 mm            | 4 0 0 × 1 0 0 × 4 0 0 mm            |
|  | 3 0 0 × 3 5 0 mm                    | 3 0 0 × 3 5 0 mm                    |
|  | - 0 . 1 MP a                        | - 0 . 1 MP a                        |
|  | 4 5 0 × 5 5 0 × 8 5 0 ( L × W × H ) | 4 5 0 × 5 5 0 × 8 5 0 ( L × W × H ) |
|  | 2 2 0 V 5 0 Hz ( 1 1 0 V )          | 2 2 0 V 5 0 Hz ( 1 1 0 V )          |