

: PMC



XRF ,

!

|                         |  |                                 |  | PMC - A       | PMC - B           | PMC - C        | PMC - D            | PMC - E                                   |
|-------------------------|--|---------------------------------|--|---------------|-------------------|----------------|--------------------|-------------------------------------------|
| PMC - F                 |  | PMC - G                         |  |               |                   |                |                    |                                           |
| ASS/ + 17               |  | : Cr 12MoV                      |  |               |                   |                |                    |                                           |
| HRC68 - HRC70           |  | HRC60 - HRC62                   |  | 3 4 5 6       | 7 8 9 10 11 12 13 | 15 16 20 22    | 28 30 35 40        | 50 60 70mm (M)                            |
| 80 90 100mm (M)         |  | 120 150 (M)                     |  | 20mm (N)      | 30mm (N)          | 40mm (N)       | 45mm (N)           | 55 60 65mm (N)                            |
| 65mm (N)                |  | 65mm (N)                        |  | 43 * 78mm (L) | 43 * 93mm (L)     | 53 * 120mm (L) | 73 * 133mm (L * H) | 88 * 150mm 98 * 180mm 108 * 180mm (L * H) |
| 118 * 150mm * 180mm 138 |  | 168 * 180mm 218 * 180mm (L * H) |  | 0.55Kg        | 0.67Kg            | 1.34Kg         | 2.9Kg              | 5.1Kg 7.3Kg 9Kg                           |
| 11.5Kg 14Kg 30Kg 40Kg   |  |                                 |  |               |                   |                |                    |                                           |