

X r f

K b r F t i r

: PCPE



	PCPE - 20T	PCPE - 30T	PCPE - 40T	PCPE - 60T
	0 - 20T (0 - 28MPa)	0 - 30T (0 - 31.5MPa)	0 - 40T (0 - 30MPa)	0 - 60T (0 - 33MPa)
	95mm (d)	110mm (d)	130mm (d)	150mm (d)
	0.00 - 40.00 MPa	0.00 - 40.00 MPa	0.00 - 40.00 MPa	0.00 - 40.00 MPa
(T)	30mm ()	40mm ()	50mm ()	50mm ()
	1MPa / 10	1MPa / 10	1MPa / 10	1MPa / 10
	/	/	/	/
	/	/	/	/
	105mm (D)	120mm (D)	140mm (D)	160mm (D)
	4	4	4	4
	80×150mm (M×N)	92×160mm (M×N)	115×185mm (M×N)	185×250mm (M×N)
	245×415×415mm (L×W×H)	275×430×420mm (L×W×H)	295×450×500mm (L×W×H)	405×470×565mm (L×W×H)
	220V (50Hz / 60Hz)	220V (50Hz / 60Hz)	220V (50Hz / 60Hz)	220V (50Hz / 60Hz)
	58Kg	72Kg	92Kg	140Kg

1 []	1.41 [MPa]
2 []	2.82 [MPa]
3 []	4.23 [MPa]
5 []	7.06 [MPa]
8 []	11.3 [MPa]

10 []	14.1 [MPa]
12 []	17 [MPa]
15 []	22.6 [MPa]
20 []	28 [MPa]
: 35 MPa	