

: P C B P



	PCBP - 2 T ()		PCBP - 1 . 5 T ()
	0 - 2 T (0 - 25MPa)		50 - 1500kg
	32mm (d)		-
			0 - 999
	CR20	LCD	4 . 3 LCD
	CR16 , CR20 , CR24 , CR30option		CR16 , CR20 , CR24 , CR30
	0 . 8 - 1 . 2		CR16 , CR20 , CR24 , CR30
	CR16 , CR20 , CR24		CR20
			220x240x380 (L X W X H)
	210×165×290mm (L × W × H)		220V (50Hz / 60Hz)
	12Kg		35kg