

: PCES



	PCES - 40T	PCES - 65T	PCES - 100T	PCES - 150T	PCES - 200T
	0 - 40	0 - 65	1 - 100	1 - 150	1 - 200
	130mm (d)	160mm (d)	200mm (d)	250mm (d)	290mm (d)
	7 LCD	7 LCD	7 LCD	7 LCD	7 LCD
	(50mm	50mm	50mm	50mm	50mm
	160×300mm (M×N)	220×300mm (M×N)	260×250mm (M×N)	285×290mm (M×N)	290×300mm (M×N)
	500×700×800mm (L	580×700×800mm (L	850×500×950mm (L	950×600×1000mm (L	1000×650×1050mm (L×W×H)
	1500W (220V / 110V	1500w (220v / 110v	1500w (220V / 110V	1500w (220V / 110V)	1500W (220V / 110V)
	200kg	280kg	520kg	620kg	850kg