

: P C S M



	PCSM - 30 T 3030	PCSM - 40 T 4040
	0 - 30 . 0	0 - 40 . 0
	130mm (d)	130mm (d)
	- 300 . 0 C / 500 . 0 C	- 300 . 0 C
	[]	[]
	300×300mm (M×N)	400×400mm (M×N)
	380×350X600mm (K×P×H)	500×480×650 (K×P×H)
	700×400×600mm (L×W×H)	800×480×650 (L×W×H)
	3000W (220V / 110V)	5000W (220V / 110V)
	260 Kg	460 Kg