

: PC 2 N



. CR 2 0 3 2 , LR 4 4

	PC - 2 N
	0 - 2 T (0 - 25 MP a)
	3 2 mm (d)
	CR 2 0
	CR 1 6 , CR 2 0 , CR 2 4 , CR 3 0
	0 . 8 - 1 . 2
	CR 1 6 , CR 2 0 , CR 2 4 , CR 3 0
	0 . 4
	2 1 0 * 1 6 5 * 2 9 0 mm (L X * W * H)
	1 2 K g