

: PCY



	PCY - 5T1212	PCY - 10T1818	PCY - 10T2020	PCY - 15T3030
	0 - 5.0	0 - 10.0	0 - 10.0	0 - 15.0
	50mm (d)	65mm (d)	65mm (d)	95mm (d)
	- 300.0C / 500.0C			
	[]	[]	[]	[]
	120×120mm (M×N)	180×180mm (M×N)	200×200mm (M×N)	300×300mm (M×N)
	140×140×60mm	180×180×60mm	200×200×60mm	300×300×65mm
	250×230×390mm (L×W×H)	290×290×420mm (L×W×H)	320×290×420mm (L×W×H)	450×420×450mm (L×W×H)
	700W(220V/110V)	1000W(220V/110V)	1200W(220V/110V)	3000W(220V/110V)
	55 Kg	90 Kg	95Kg	180Kg