

: P C M P



|       | PCMP - 2 T                       | PCMP - 5 T                       | PCMP - 12 T                      | PCMP - 15 T                      | PCMP - 24 T                      | PCMP - 30 T                      | PCMP - 40 T                      |
|-------|----------------------------------|----------------------------------|----------------------------------|----------------------------------|----------------------------------|----------------------------------|----------------------------------|
|       | 0 - 2 T ( 25MPa )                | 0 - 5 T ( 0 - 31 . 4 MPa )       | 0 - 12 T ( 0 - 30 MPa )          | 0 - 15 T ( 0 - 30 MPa )          | 0 - 24 T ( 0 - 34 MPa )          | 0 - 30 T ( 0 - 31 . 1 MPa )      | 0 - 40 T ( 0 - 30 MPa )          |
|       | 32 mm ( d )                      | 45 mm ( d )                      | 70 mm ( d )                      | 80 mm ( d )                      | 95 mm ( d )                      | 110 mm ( d )                     | 130 mm ( d )                     |
|       | , , , , , , ,                    |                                  |                                  |                                  |                                  |                                  |                                  |
|       |                                  |                                  |                                  |                                  |                                  |                                  |                                  |
| ( T ) | 30 mm                            | 30 mm                            | 30 mm                            | 30 mm                            | 30 mm                            | 40 mm                            | 50 mm                            |
|       | 1 MPa / 10                       | 1 MPa / 10                       | 1 MPa / 10                       | 1 MPa / 10                       | 1 MPa / 10                       | 1 MPa / 10                       | 1 MPa / 10                       |
|       | 50 mm ( D )                      | 80 mm ( D )                      | 80 mm ( D )                      | 90 mm ( D )                      | 105 mm ( D )                     | 120 mm ( D )                     | 140 mm ( D )                     |
|       | 2                                | 2                                | 2                                | 2                                | Four                             | Four                             | Four                             |
|       | 85 × 120 mm ( M × H )            | 96 × 130 mm ( M × H )            | 96 × 130 mm ( M × H )            | 140 × 150 mm ( M × H )           | 80 × 150 mm ( M × H )            | 92 × 160 mm ( M × H )            | 106 × 185 mm ( M × N )           |
|       | 210 × 150 × 350 mm ( L × W × H ) | 225 × 155 × 380 mm ( L × W × H ) | 225 × 155 × 380 mm ( L × W × H ) | 245 × 175 × 390 mm ( L × W × H ) | 245 × 175 × 415 mm ( L × W × H ) | 275 × 195 × 420 mm ( L × W × H ) | 295 × 215 × 500 mm ( L × W × H ) |
|       | 12 Kg                            | 28 Kg                            | 28 Kg                            | 38 Kg                            | 42 Kg                            | 56 Kg                            | 75 Kg                            |