

: PCF



	PCF - 15T	PCF - 24T	PCF - 30T	PCF - 40T	PCF - 60T
	0 - 15T (0 - 30 MP a)	0 - 24T (0 - 34 MP a)	0 - 30T (0 - 31 . 5 MP	0 - 40T (0 - 30 MP a)	0 - 60T (0 - 34 MP a)
	80mm(d)	95mm(d)	110mm(d)	130mm (d)	150mm (d)
" (T) "	30mm	30mm	40mm	50mm	50mm
	()	()	()	()	()
	1 MP a / 10				
	90mm(D)	105mm (D)	120mm (D)	140mm (D)	160mm(D)
	4	4	4	4	Four
	80 × × 130 mm(M× N)	112 × 160 mm(M× N)	112 × 160 mm(M× N)	126 × 185 mm(M× N)	185 × 250 mm(M× N)
	260 × 175 × 395 mm(H)	305 × 195 × 425 mm(H)	305 × 195 × 425 mm(H)	355 × 215 × 505 mm(H)	405 × 240 × 565 mm(L × W× H)
	42 Kg	65 Kg	65 Kg	90 Kg	120 Kg

()	(MP a)
1	0 . 75
3	2 . 2
5	3 . 7
10	7 . 5
12	9
15	11 . 3
20	15
30	22 . 5

40

30

: 3.5 MPa