

: PCI H



( W I P ) . A S M E

1 0 0 ° C

	PCI H - 20T	PCI H - 40T	PCI H - 60T	PCI H - 100T
	0 - 20T	0 - 40T	0 - 60.0	0 - 100
	130mm ( d )	150mm ( d )	200mm ( d )	220mm ( d )
	1 ~ 999	1 ~ 999	1 ~ 999	1 ~ 999
	7 LCD	7 LCD	7 LCD	7 LCD
	- 200.0C	- 200.0C	- 200.0C	- 200.0C
	300MPa	300MPa	300MPa	500MPa
	30 × 150mm ( M × N )	40 × 150mm ( M × N )	50 × 150 ( M × N )	50 × 150 ( M × N )
( T )	50mm	50mm	50mm	50mm